

Fluorescent Light Kit & Accessories *FLK Series*

Features



- Light kits are offered in 18", 24" and 48" widths.
- CSA and UL component recognized.
- Operating voltage 115 AC 60Hz
- 115V AC, features a manually operated switch, 115V convenience outlet, durable plastic lens, and 6 foot power cord (without plug).
- Can mount into light mounting channel, bolt through enclosure or by using magnet strip (available separately - see chart below.)
- 1¾" high x 4½" deep.
- Finished in white.
- Use standard 18", 24" or 48" T8 fluorescent bulb (not included)
- Magnet mount
 - Can be used with mild steel enclosures only.



Accessories

- Remote Door Switches

Part No.	Description
FLK18T8¹	18" Fluorescent Light Kit 115V
FLK24T8¹	24" Fluorescent Light Kit 115V
FLK48T8¹	48" Fluorescent Light Kit 115V
FLK18MM	Magnet mount for 18" and 24" kit
FLK48MM	Magnet mount for 48" light kit

¹ T8 fluorescent bulb not included

Data subject to change without notice