

Two Post Mounting Clamping Shelf *RACS Series*



This rackshelf has been designed to provide superior ventilation for both cable and satellite boxes as well as other components that generate considerable amounts of heat. Featuring two adjustable foam padded mounting bars for securing components without fear of scratches.

Features

- Allows easy rack mounting of narrow equipment or items that do not have rack mounting capabilities.
- Includes two adjustable - gasketed (to protect from scratching the clamped equipment) horizontal clamps.
- Designed for equipment requiring front adjustment without sliding around the shelf (ie...pushbuttons, jacks, plugs, dials etc.).
- Choice of four clamp locations depending on depth of equipment.
- Choice of three shelf heights (see table below).
- Mounted equipment height should be at least 1/2" shorter than shelf "panel height" to allow clearance for the gasketed clamps (see table below).
- Provides a sturdy shelf without obstructing upward heat movement.
- Rear lip folded up for extra strength & doubles as an equipment retainer.
- 14-gauge steel construction.
- Rugged textured - black powder paint finish.
- RoHS and REACH compliant.
- Manufactured in North America.



Accessories

- Mounting Hardware
- Hook and Loop Roll

Part No.	Overall Dimensions			Rack Units	Mounting Dimensions		Max Equipment Height
	Height	Width	Depth		Height	Width	
RACSV190315BK1	3.47	19.01	15.00	2U	3.50	19.00	3.00
RACSV190515BK1	5.22	19.01	15.00	3U	5.25	19.00	4.75
RACSV190715BK1	6.47	19.01	15.00	4U	6.50	19.00	6.50

Data subject to change without notice