

BE-02+

# PROSAFE USB RECHARGEABLE BEANIE HEADLIGHT

NEW



ALSO IDEAL AS A  
HANDY KEY-FOB

**USB**  
CHARGING

**SAMSUNG**  
LED CHIP

2½-6½  
HOURS  
RUNTIME

13  
METRE  
BEAM RANGE

150  
LUMENS  
OUTPUT

IPX5  
WATER  
RESISTANCE



INTEGRATED  
MALE USB



HIGH POWERED  
150 LUMEN OUTPUT



CHARGE DIRECTLY FROM  
USB PORT - RED TO GREEN LIGHTS



SUPPLIED READY  
MERCHANTISED

- » High quality warm knitted black beanie hat with integrated USB rechargeable LED light
- » 4 x high powered cool white 6500k Samsung SMD LEDs - 150 lumen
- » 420mAh Lithium-polymer battery
- » Gives you between 2.5 and 6.5 hours of light off one charge
- » Light can easily be removed from the hat and charged directly through a USB port
- » Can be fully charged in 4 hours
- » Press once to turn on and toggle between 3 light intensity levels. HIGH > LOW > 2 Hz FLASH > OFF
- » Comfortable knitted Beanie, one size fits all
- » Material: 35% acrylic 65% polyester, machine washable at 30°
- » Ideal for: Runners, Walkers, Camping, Plumbers, Electricians, Tradesman and Contract Engineers

**BATTERY** 1 x 420 mAh Li-polymer Battery (included)  
**WEIGHT** 125g (with beanie)  
**DIMENSION** Headlight: 74 x 41 x 15mm - Beanie: W 250 x H 220 mm