

## Hinged Wall Mount Rack *APB Series*

Rugged 80 lbs Weight Capacity

### Features



- Constructed in 14-gauge steel and 10-gauge steel (rails).
- EIA-310-D compliant 10-32 tapped rails with 19" mounting.
- Double-hinged for easy rear access.
- Adjustable depth from 12" to 18" using slots for easy set-up and adjusting.
- Rear cable access with multiple tie points for cable management.
- Finished in smooth black powder paint.
- Knockdown design ships unassembled for easy handling and shipping protection.
- Includes starter pack of mounting hardware. (25-pack of 10-32 screws)
- Tested to nearly double the suggested load rating of 80 lbs (36 kg).
- RoHS Compliant.
- Manufactured in North America.

### Similar Products

- If you are looking for a taller or deeper option, consider the **HWMR Series**.
- If you are looking for an APB with a shelf included, consider the **APBS Series**.

### Gallery



### Accessories

- Universal Rack Shelf
- Outlet Strips
- Cable Management
- 10-32 Mounting Hardware
- Two Post Mounting Keyboard & Equipment Shelf
- Rack Panels
- Mounting Hardware
- Hook and Loop Roll

Part No.	Overall Dimensions		Rack Units	Mounting Dimensions			
	Height	Width		Height	Width	Min Depth	Max Depth
<b>APB19007BK1</b>	6.98	19.25	4U	7.00	19.00	12.00	18.00
<b>APB19010BK1</b>	10.48	19.25	6U	10.50	19.00	12.00	18.00
<b>APB19014BK1</b>	13.98	19.25	8U	14.00	19.00	12.00	18.00
<b>APB19021BK1</b>	20.98	19.25	12U	21.00	19.00	12.00	18.00

Tags: **Hinged Panel Mount, Adjustable Panel Bracket**

*Data subject to change without notice*

© 2016. Hammond Manufacturing Ltd. All rights reserved.