

H664DS

SWITCH FUSIBLE HD 600V 200A 6P NEMA44X5

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Single Throw Safety Switch
Line Rated Current	200 A
Product certifications	UL listed
NEMA degree of protection	NEMA 3/3R4/4X/12 stainless steel 304
Device composition	None
Disconnect device type	Fusible disconnect
Short-circuit current	200 kA R, J or L 10 kA H or K
Device mounting	Surface
Number of poles	6
Electrical connection	Lugs
Series name	Heavy duty
System Voltage	600 V AC
AWG gauge	AWG 6...250 kcmil (copper or aluminium)

Ordering and shipping details

Category	00115 - H&HU SW,4&6P,N4,SS 30-200A
Discount Schedule	DE1
GTIN	00785901369585
Nbr. of units in pkg.	1
Package weight(Lbs)	10
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Not Green Premium product
--------------------------	---------------------------

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Contractual warranty	
Warranty period	18 months