

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0008500106
Status: Active
Overview: KK® Interconnect System - Molex
Description: KK® 396 Crimp Terminal 2478, 18-24 AWG, Bag, Brass Tin (Sn)

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-08-50-001 \(PDF\)](#)
[Packaging Specification PK-2759-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Crimp Terminals
Series 2478
Application Power
Crimp Quality Equipment Yes
MolexKits Yes
Overview KK® Interconnect System - Molex
Packaging Alternative 08-50-0105 (Reel)
Product Name KK® 396, KK® 508
UPC 800753750029

Physical
Gender Female
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 0.280/g
Packaging Type Bag
Plating min - Mating 2.540µm
Plating min - Termination 2.540µm
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 2.79mm max.
Wire Size AWG 18, 20, 22, 24
Wire Size mm² N/A

Solder Process Data
Lead-freeProcess Capability N/A

Material Info
Engineering Number 2478-1-(P909)L

Reference - Drawing Numbers
Packaging Specification PK-2759-001
Product Specification PS-08-50-001
Sales Drawing SD-2478



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/21/2016 (20 June 2016)	
Halogen-Free	
Status	
Low-Halogen	

Need more information on product environmental compliance?
Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[2478](#) Series

Use With
[2574](#) , [2139](#) , [41695](#) , [3069](#) , [6422](#) , [5265](#) , [5239](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION