

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0430251800
Status: Active
Overview: Micro-Fit 3.0™ Connectors
Description: Micro-Fit 3.0™ Receptacle Housing, Dual Row, 18 Circuits, UL 94V-0, Low-Halogen, Black

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-43045 \(PDF\)](#)
[Product Specification TS-43045-001-001 \(PDF\)](#)
[Product Specification TS-46235-001-001 \(PDF\)](#)
[Packaging Specification PK-43025-001-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)
[Product Literature \(PDF\)](#)

Agency Certification
CSA LR19980
UL E29179

General
Product Family Crimp Housings
Series 43025
Application Power, Wire-to-Board, Wire-to-Wire
Overview Micro-Fit 3.0™ Connectors
Product Literature Order No 987650-5984
Product Name Micro-Fit 3.0™
UPC 800754369053

Physical
Circuits (maximum) 18
Color - Resin Black
Flammability 94V-0
Gender Female
Glow-Wire Compliant No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin Nylon
Net Weight 1.852/g
Number of Rows 2
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 3.00mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40°C to +105°C

Solder Process Data
Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers
Packaging Specification PK-43025-001-001
Product Specification PS-43045, TS-43045-001-001, TS-46235-001-001
Sales Drawing SDA-43025-****, SDES-43025-1000



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per - ED/21/2016 (20 June 2016)
Halogen-Free Status
Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
43025 Series

Mates With
Micro-Fit 3.0™ Plug Housings 43020 ,
Micro-Fit 3.0™ Headers 43045 , Micro-Fit 3.0™ Test Plug 44242

Use With
Micro-Fit 3.0™ Female Crimp Terminals 43030 , 45773 , Micro-Fit RMF™ Female Crimp Terminals 46235