

Instrument cases/system enclosures

Ripac Vario-Module accessories



Front flanges

Required when the Ripac Vario-Module is to be used as a rack-mounted enclosure. The flanges have a channel to accommodate vertical EMC gaskets.

Material:
Aluminium, clear-chromated

U	Packs of	Model No. VM	
		without handle hole	with handle hole
3	2	3981.210	3981.260
4	2	3981.220	3981.270
6	2	3981.230	3981.280
7	2	3981.240	3981.290

+ Accessories:

EMC gaskets, vertical, see page 506.
Front handles for mounting on front flanges, see page 497.



Front corner trims

Required when the Ripac Vario-Module is to be used as a desk-top case. The corner trims have a channel to accommodate vertical EMC gaskets.

Material:
Die-cast zinc
Colour:
RAL 7035

U	Packs of	Model No. VM
1	2	3981.570
2	2	3981.300
3	2	3981.310
4	2	3981.320
6	2	3981.330
7	2	3981.340
8	2	3981.590

+ Accessories:

Vertical EMC gaskets, see page 506.
Front handles for mounting on front corner trim pieces, see page 560.



Front handles

For mounting on front corner trims

Maximum load capacity: 500 N

Material:
Cover: ABS
Handle part: Aluminium, clear-anodised.

Supply includes:
2 handle parts, 4 covers, assembly parts.

U	Packs of	Model No. VM
3	2	3982.350
4	2	3982.360
6	2	3982.400
7	2	3982.410



Carrying handles

For ergonomic transportation, even with stacked enclosures.

May also be used as a support stand.

Max. load capacity: 350 N.

Material:
Die-cast zinc and extruded aluminium section

Colour:
RAL 7035

Note:
Only for use with front and rear trims.

For enclosure depth	Packs of	Model No. VM
250.4 mm	2	3981.350
310.4 mm	2	3981.360
370.4 mm	2	3981.370
430.4 mm	2	3981.380