



## Vimtag | 960P/1080P CAMERA

### KEY FEATURES

Wireless smart sensor (SOS button, door sensor, etc)  
 Face identification  
 Two-way audio  
 Wi-Fi connection  
 Android, IOS devices, remote real-time monitoring  
 Multi-user access, multi-device management  
 Motion detection/alarm/snapshot/video  
 64G Micro SD card / cloud box storage  
 PTZ remotely operated

SPECIFICATION	P1	P1-S
CAMERA		
Image Sensor	1/3 "color CMOS sensor	1/2.7"color CMOS sensor
Display resolution	1280*960(1.3Mega pixels)	1920*1080(2.0Mega pixels)
Lens	f: 6mm, F:2.4 3.0Mega pixels	
Visual angle	H:48°; V:36°; D:60°	H:52°; V:39°; D:65°
Min illumination	0.1Lux(IR LED OFF)	
AUDIO		
Input/Output	Built-in microphone and speaker	
Audio Compression	AAC	
Video		
Video Compression	H.264	
Lighting frequency	50Hz, 60Hz	
Frame rate	25fps	
Resolution	1.3Mega Pixels	2.0Mega Pixels
Image adjustment	Brightness, Contrast, Saturation, Sharpness	
White balance BLC	Automatically	
Night vision	2 pcs matrix infrared lights, IR distance: 10 meters	
Network		
Wireless networks	WIFI(IEEE802.12b/g/n),internal antenna	
Ethernet	10/100Mbps	
Protocols	TCP/IP/UDP/IP/HTTP/DHCP/RTMP/MUTP	
IP address	Static IP address and dynamic IP address	
Support connecting RF devices	Support 433MHZ/315MHZ/866MHZ RF devices	
ALARM		
Alarm detection	Motion detection	
Alarm linkage	Snapshot, audio/video record, RF alarm devices	
Alarm notification	Real-time App push notifications	
RF Peripheral	RF alarm Peripheral	
General		
Power	DC 5V / 2.0 A,USB interface, power consumption < 8W	
Network interface	Micro USB3.0 and a special adapter	
Adjustable lens	NO	
LED intructions	Network signal	
Video Storage	Micro SD Card* (maximum 64GB),cloud box, cloud storage	
Work temperature	0° ~ 55°C (32°F ~ 131°F)	
Work humidity	10% ~ 80% (No condensation)	
Storage temperature	10°C ~ 60° (14°F ~ 140°F)	
Storage humidity	0% ~ 90%(No condensation)	
Colour	White, Silver	
Size (L*W*H)	91(L) x90(W) x121mm(H)	
Weight	340g	
Certificate	RoHS,CE,FCC,NCC	

(\*Micro SD Card NOT supplied)