

---

## Supported Operating Systems

Operating system	Windows 10 Pro 64
------------------	-------------------

---

### Processor

Chipset	Intel® H110
Processor speed	3.2 GHz
Processor family	6th Generation Intel® Core™ i5 processor
Processor	Intel® Core™ i5-6500 with Intel HD Graphics 530 (3.2 GHz, up to 3.6 GHz with Intel Turbo Boost, 6 MB cache, 4 cores)

---

### Drives

Hard drive description	500 GB 7200 rpm SATA
Optical drive	Slim SATA DVD-Writer
External drive bays	One Slim ODD (optional) 1 SD reader
Internal drive bays	One 3,5 cm (2.5") HDD One 8,9 cm (3.5") HDD
Storage type	HDD

---

### Graphic Subsystem

Graphics	Intel® HD Graphics 530
Graphics	Integrated

---

### Multimedia

Audio	HD audio with Realtek ALC3252 codec, combo microphone/headphone jack and 3.5 mm line-out and line-in ports
-------	------------------------------------------------------------------------------------------------------------

---

### Input devices

Keyboard	HP USB Keyboard
Pointing device	HP USB Mouse

---

### Connectivity and Communications

Network interface	Integrated Realtek RTL8111HSH-CG GbE
Ports	2 USB 3.0 1 microphone/headphone combo
Expansion slots	1 PCIe x1 1 PCIe x16
I/O Port location	Front
Ports	6 USB 2.0 1 audio line in 1 audio line out 1 HDMI 1 VGA 1 RJ-45
I/O Port location	Back

---

### Battery and Power

Power 180 W, up to 85% efficient, active PFC

---

### Weights

Weight 3.66 kg

---

### System Components

Form factor Small form factor

---

### Security Management

Security management Trusted Platform Module (TPM) 2.0 (firmware)  
Security cable slot

---

### Software and Applications

Software HP business PCs are shipped with a variety of software titles including Cyberlink Power Media Player, Cyberlink Power2Go (secure burn), HP ePrint Driver, HP Recovery Manager and HP Support Assistant. Please refer to this product's quick spec document for a full list of preinstalled software.

Software footnote number [8]

---

### Dimensions

Minimum dimensions (W x D x H) 270 x 290 x 100 mm

---

### Memory

Memory, standard 4 GB DDR4-2133 SDRAM (1 x 4 GB)

Memory slots 2 DIMM

Standard memory note Transfer rates up to 2133 MT/s

Memory and storage 4 GB memory  
500 GB HDD storage

---

### Warranty

Warranty On-site warranty: One-year (1-1-1) limited warranty delivers one year of on-site, next business day service for parts and labor and includes free telephone support 24 x 7. One-year onsite and labor are not available in all countries. Service offers terms up to 5 years by choosing a Care Pack. To choose the right level of service for your HP product, visit HP Care Pack Central: [www.hp.com/go/cpc](http://www.hp.com/go/cpc)

---