

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0016020098

Status:

Active

Overview:

C-Grid® Products

Description:

SL™ Crimp Terminal 70058, 24-30 AWG, Bag Selective Gold (Au)



Series image - Reference only

Documents:

[Drawing \(PDF\)](#)

[Product Specification PS-70058-001 \(PDF\)](#)

[Product Specification PS-70400-001 \(PDF\)](#)

[Product Specification TS-70058-001-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family

Series

Application

Comments

Crimp Quality Equipment

Overview

Packaging Alternative

Product Name

UPC

Crimp Terminals

70058

Signal

Use with CyClone Panel-to-Panel Connector 73099

Yes

C-Grid® Products

16-02-0083 (Reel)

SL™

800753596054

Physical

Gender

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Plating min - Mating

Plating min - Termination

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

Female

Phosphor Bronze

Gold

Tin

0.071/g

Bag

0.762µm

1.270µm

Crimp or Compression

1.52mm max.

24, 26, 28, 30

N/A

Material Info

Engineering Number

70058-0208

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-70058-001, PS-70400-001, TS-70058-001-001

SD-70058-0208

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per

-ED/01/2017 (12

January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

70058 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION