

## HAMEG® HZ154

Probe 1:1 / 10:1



Product type    Probe 1:1 / 10:1

### Key Facts

HZ154

### Probe 1:1 / 10:1

Attenuation ratio	1:1
Switchable	10:1
Bandwidth	10/100MHz
Rise time	< 35/3.5 ns
Input impedance	1/10 M $\Omega$    82/12 pF
Max. voltage	(10:1) 600 V (DC + peak AC)
LF compensation	1 at 10:1
RF compensation	2 at 10:1
Cable length	1.2 m
Measuring category	CAT I