


Specification

Photo		
Capacity	2GB-16GB	
Color	Black with transparent cap	
Interface	USB 2.0 certified, backward compatible with USB 1.1 True "plug & play" supports hot swapping function	
Power Supply	USB Bus-Powered; No external power required	
Systems Supported	Windows 10/8.1/8/7/XP Mac OS 10.4.X or above Linux 2.6.X or above	
LED Indication		
Operating Temperature	0° C to +60° C (32° F to 140° F)	
Storage Temperature	-20° C to +60° C (-4° F to +140° F)	
Dimensions	(L) 55.3 x (W) 18.1 x (H) 8.7 mm	
Weight	8g approx.	