

General Information

Extended Product Type:	MCB-11
Product ID:	1SFA611610R1011
EAN:	7320500307779
Catalog Description:	MCB-11 Contact block
Long Description:	Modular contact block

Additional Information

ABB Industrial IT Suite:	Control IT
Accessory Type:	Contact blocks and holders
Block:	Double contact block
Country of Origin:	Sweden (SE)
Customs Tariff Number:	85369001
Data Sheet, Technical Information:	1SFC151003C0201
Declaration of Conformity - CE:	1SFA1-83
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20
E-nummer:	3714017
EAN:	7320500307779
ETIM 4:	EC002024 - Accessories for control circuit devices
ETIM 5:	EC000041 - Auxiliary contact block
ETIM 6:	EC000041 - Auxiliary contact block
Environmental Information:	1SFC151010D0201
Function:	Without holder
IT Publishing Status:	Level 0 - Information enabled
Illumination:	Non-illuminated
Industrial IT Certification Level:	0
Instructions and Manuals:	1SFC151003C0201
Invoice Description:	CONTACT BLOCK#MCB-11
Mechanical Durability:	10 million
Minimum Order Quantity:	10 piece
Mounting Positions:	Front mounting
Number of Auxiliary Contacts NC:	1
Number of Auxiliary Contacts NO:	1
Object Classification Code:	S
Package Level 1 Gross Weight:	0.04 kg
Package Level 1 Height:	0.02 m
Package Level 1 Length:	0.15 m
Package Level 1 Units:	10 piece
Package Level 1 Width:	0.11 m
Product Main Type:	MCB
Product Name:	Contact block
Product Net Depth:	0.028 m
Product Net Height:	0.020 m
Product Net Weight:	0.04 kg
Product Net Width:	0.044 m
Product Range:	Modular range

Product Type:	MCB
Rated Frequency (f):	Supply Circuit 50 Hz Supply Circuit 60 Hz
Rated Operational Current AC-15 (I_e):	(24 / 127 V) 8 A (220 / 240 V) 6 A
Rated Operational Current DC-13 (I_e):	(24 V) 5 A (125 V) 1.1 A
RoHS Date:	0635 4
RoHS Information:	1SFC151011D0203
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Selling Unit of Measure:	piece
Short Description:	CONTACT BLOCK#MCB-11
Suitable For:	MP1 MP2 MP3 MP4 MPD1 MPD2 MPD3 MPD4 MPD5 MPD11 MPD12 MPD13 MPD14 MPD15 MPD16 MPM1 MPM2 KP6 MPET3 MPEP3 MPEK3 MPET4 MPEP4 MPEK4 MPMT3 MPMT4 MPMP3 MPMP4 M2SS1 M2SS2 M2SS3 M2SS4 M2SS5 M2SS6 M3SS1 M3SS2 M3SS3 M3SS4 M3SS5 M3SS6 M3SS7 M3SS8 M3SSC1 M3SSC2 M3SSC3 M3SSC4 M3SSC5 M3SSC6 M3SSC7 M3SSC8

M2SSK1
M2SSK2
M2SSK3
M3SSK1
M3SSK2
M3SSK3
MTS1
MTS2
MTS3
MJS1
MJS2
MJS5
MJS6
MJS7
MJS8
MJS11
MJS12

UNSPSC: 39121500

