

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0355070300

Status:

Active

Overview:

Sherlock™ Connector System

Description:

2.00mm Pitch Sherlock™ Wire-to-Board Housing, Natural, 3 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-35507-001-001 (PDF)

Product Specification PS-35507-002-001 (PDF)

Product Specification PS-35507-003-001 (PDF)

Packaging Specification PK-35507-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

Crimp Housings

Series

35507

Application

Signal, Wire-to-Board

MolexKits

Yes

Overview

Sherlock™ Connector System

Product Name

Sherlock™

UPC

800753877610

Physical

Circuits (maximum)

3

Circuits Detail

3

Color - Resin

Natural

Flammability

94V-0

Gender

Female

Glow-Wire Compliant

No

Keying to Mating Part

None

Lock to Mating Part

Yes

Material - Resin

Polyester

Net Weight

0.193/g

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

2.00mm

Polarized to Mating Part

Yes

Stackable

No

Temperature Range - Operating

-40°C to +105°C

Electrical

Current - Maximum per Contact

2.0A

Material Info

Reference - Drawing Numbers

Packaging Specification


PK-35507-001

Product Specification

PS-35507-001-001, PS-35507-002-001, PS-35507-003-001

Sales Drawing

SD-35507-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[35507](#) Series

Mates With

Sherlock™ Wire-to-Board Header [35362](#) ,
[35363](#)

Use With

2.00mm Pitch Crimp Terminal [50212](#)