

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0022013107](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: [KK® 254 Crimp Housing, Friction Ramp, 10 Circuits](#)

Documents:

[3D Model](#) [Packaging Specification PK-2695-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-10-07-001 \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Crimp Housings
 Series [2695](#)
 Application Signal, Wire-to-Board
 Overview [KK® Interconnect System - Molex](#)
 Product Name KK® 254
 UPC 800753593909

Physical

Circuits (maximum) 10
 Color - Resin Natural (White)
 Flammability 94V-0
 Gender Female
 Glow-Wire Compliant No
 Lock to Mating Part Yes
 Material - Resin Nylon
 Net Weight 1.080/g
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 2.54mm
 Pitch - Termination Interface 2.54mm
 Polarized to Mating Part Yes
 Stackable No
 Temperature Range - Operating See Product Specification

Solder Process Data


Lead-freeProcess Capability N/A

Material Info

Engineering Number 2695-10RP

Reference - Drawing Numbers

Packaging Specification PK-2695-001-001
 Product Specification PS-10-07-001
 Sales Drawing SD-2695



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/01/2017 (12
 January 2017)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[2695 Series](#)

Mates With

KK®254 PCB Headers [42375](#) , [42377](#)
 , [42376](#) , [4030](#) , [6373](#) , [6410](#) , [171856](#) ,
[171857](#)

Use With

[2759](#) , [4809](#) KK® Crimp terminal