

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0847020006](#)  
**Status:** **Active**  
**Overview:** [Brad® Industrial Ethernet Solutions](#)  
**Description:** Receptacle, RJ-45, Punchdown Panel Mount Receptacle Jack

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Receptacles
Series	<a href="#">84702</a>
IP Rating	IP67
MolexKits	Yes
Overview	<a href="#">Brad® Industrial Ethernet Solutions</a>
Product Name	RJ45
Type	110 Punchdown
UPC	822348263059

**Physical**

Coupling Type	External Thread
Gender	Male
Keyway	None
Length	N/A
Material - Component	ABS
Mounting Thread Size	1" - 14 UNC
Orientation	Straight
Panel Mount	Front
Poles	N/A
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	N/A
Wire/Cable Type	N/A

**Electrical**

Current - Maximum per Contact	1.5A
Voltage - Maximum	125V

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	SD-84702-004
---------------	--------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[84702](#) Series

**Mates With**

[84700-0002](#) Plug, [84702](#) Cable Assemblies

**Use With**

[84700-0003](#) Dust Cover