

Wall Mount Switch Mode Power Supplies

Wall mounted light weight and compact Switch Mode Power Supply Units with a wide 90V-264V AC input voltage range to suit travel product applications. The narrow width (excluding the 30G Series) allows two adaptors to be used in a standard double power outlet. Insulated active and neutral pins meet AS/NZS3112 for improved electrical safety. Electrical Safety Authority Approved. Popular models are shown in the table below. Other voltages and choice of output plug can be custom made upon request.

05G Series



Dimensions: 41(W) x 57(H) x 49(D)mm
Maximum output power: 5W

10G Series



Dimensions: 41(W) x 74(H) x 35(D)mm
Maximum output power: 10-12W

12J Series



Dimensions: 39(W) x 79(H) x 38(D)mm
Maximum output power: 12W

new

15G Series



Dimensions: 44(W) x 85(H) x 36(D)mm
Maximum output power: 15-18W

18J Series



Dimensions: 39(W) x 79(H) x 38(D)mm
Maximum output power: 18W

new

30G Series



Dimensions: 55(W) x 96(H) x 42(D)mm
Maximum output power: 30W

CAT #	OUTPUT	PLUG	CENTRE	HOUSING
T0333-21G	3.3V DC 3.0A	11 x 5.5 x 2.1mm	Pos	15G
T0510-003	5V DC 1.0A	10 x 3.5 x 1.3mm	Pos	05G
T0510-001	5V DC 1.0A	11 x 5.5 x 2.1mm	Pos	05G
T0510-002	5V DC 1.0A	Mini-USB		05G
T0520-13G	5V DC 2.0A	10 x 3.5 x 1.3mm	Pos	10G
T0520-21G	5V DC 2.0A	11 x 5.5 x 2.1mm	Pos	10G
T0530-21N	5V DC 3.0A	11 x 5.5 x 2.1mm	Neg	15G
T0530-21G	5V DC 3.0A	11 x 5.5 x 2.1mm	Pos	15G
T0530-25G	5V DC 3.0A	11 x 5.5 x 2.5mm	Pos	15G
T0532-002	5.4V DC 3.2A	9.5 x 4.0 x 1.7mm	Pos	30G
T0683-003	6V DC 830mA	10 x 3.5 x 1.3mm	Pos	05G
T0683-002	6V DC 830mA	11 x 5.5 x 2.1mm	Neg	05G
T0683-001	6V DC 830mA	11 x 5.5 x 2.1mm	Pos	05G
T0620-21G	6V DC 1.67A	11 x 5.5 x 2.1mm	Pos	10G
T0625-21G	6V DC 2.5A	11 x 5.5 x 2.1mm	Pos	15G
T0713-21G	7.5V DC 1.33A	11 x 5.5 x 2.1mm	Pos	10G
T0752-21G	7.5V DC 2.0A	11 x 5.5 x 2.1mm	Pos	15G
T0955-13G	9V DC 550mA	10 x 3.5 x 1.3mm	Pos	05G
T0955-003	9V DC 550mA	11 x 5.5 x 2.1mm	Neg	05G
T0955-001	9V DC 550mA	11 x 5.5 x 2.1mm	Pos	05G
T0955-002	9V DC 550mA	11 x 5.5 x 2.5mm	Pos	05G

CAT #	OUTPUT	PLUG	CENTRE	HOUSING
T0911-21G	9 DC 1.1A	11 x 5.5 x 2.1mm	Pos	10G
T0916-21G	9V DC 1.66A	11 x 5.5 x 2.1mm	Pos	15G
T0927-21G	9V DC 2.7A	11 x 5.5 x 2.1mm	Pos	30G
T1241-001	12V DC 410mA	11 x 5.5 x 2.1mm	Pos	05G
T1210-13G	12V DC 1.0A	10 x 3.5 x 1.3mm	Pos	10G
T1210-21G	12V DC 1.0A	11 x 5.5 x 2.1mm	Pos	10G
T1210-25G	12V DC 1.0A	11 x 5.5 x 2.5mm	Pos	10G
T1210-21J	12V DC 1.0A	12 x 5.5 x 2.1mm	Pos	12J
T1255-21N	12V DC 1.5A	11 x 5.5 x 2.1mm	Neg	15G
T1255-21G	12V DC 1.5A	11 x 5.5 x 2.1mm	Pos	15G
T1255-25G	12V DC 1.5A	11 x 5.5 x 2.5mm	Pos	15G
T1255-21J	12V DC 1.5A	13 x 5.5 x 2.1mm	Pos	18J
T1225-21G	12V DC 2.5A	11 x 5.5 x 2.1mm	Pos	30G
T1512-21G	15V DC 1.2A	11 x 5.5 x 2.1mm	Pos	15G
T1512-005	15V DC 1.2A	EIAJ-05	Pos	15G
T1516-25G	15V DC 1.6A	10 x 5.5 x 2.5mm	Pos	30G
T1866-21G	18V DC 660mA	11 x 5.5 x 2.1mm	Pos	10G
T1810-21G	18V DC 1.0A	11 x 5.5 x 2.1mm	Pos	15G
T1810-25G	18V DC 1.0A	11 x 5.5 x 2.5mm	Pos	15G
T1816-001	18V DC 1.6A	F-Type Connector	Pos	30G
T2412-21G	24V DC 1.2A	11 x 5.5 x 2.1mm	Pos	30G