



MATERIALS:

Lower Contacts: .025 thick Beryllium Copper per QQ-C-533, Alloy 172, HM.

Upper Contacts: .025 thick Phosphor Bronze, Alloy 510, Grade A

RATINGS:

Operating Temperature: +102°C. (+215°F.)

Operating Voltage: 500 VRMS

Current: 1 Amperes

ORDERING INFORMATION: Model 5515A

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA