

Detailed View

Farnell Order Code: 146-6995

71.35.313 **Vibration Mount, cylindrical /
Inside and Outside Thread**

Lenght 6,0 mm
Material Rubber
Coulor zinc plated
UL-Rating M3
Slot Depths 6,0 mm
Slot Width 3,0 mm
Model In-Outside Thread
Width 8,0 mm
Design Grade of Hardness 55-57°
RoHS compliant

