

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192030005](#)
Status: **Active**
Overview: [High-Temperature Temp Terms Terminals and Splices](#)
Description: Krimptite™ Temp-Term Ring Tongue Terminal for 18 to 22 AWG Wire, Stud Size 1/4" (M6), Mylar Tape Carrier

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-015-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19203
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	High-Temperature Temp Terms Terminals and Splices
Product Name	Krimptite™, Temp-Terms
Type	Ring
UPC	800753049369
Physical	
Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.804/g
Packaging Type	Adhesive Tape on Reel
Stud Size	1/4" (M6)
Wire Size AWG	18, 20, 22
Wire Size mm²	0.25-1.50
Material Info	
Engineering Number	A-S-122-14T
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001, PS-19902-015-001
Sales Drawing	SD-19203-036



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant REACH SVHC Not Contained Per -ED/01/2017 (12 January 2017) Halogen-Free Status Low-Halogen	China RoHS
--	-------------------

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[19203](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION