

8100 SC 2 Zyklop Speed ratchet set, 1/2" drive, metric, 37 pieces
1/2" drive, metric



EAN	4013288121189	Dimension:	365x70x310 mm
Code:	05003645001	Weight:	5838,4 g
Article-No.		Country of origin:	CZ
		Customs tariff no.:	82041200

- Combines five different types of a ratchet in one
- 37-piece set in a robust metal case
- Freely pivoting ratchet head
- Take it easy Tool Finder: colour coding according to profile and size

37-piece Zyklop set in robust metal case: Zyklop ratchet with 1/2" drive. The 72 fine-pitched teeth enable a low return angle of only 5°. The ratchet head pivots freely and can be locked into any position by using the slide switch that is positioned on either side. It is even possible to work conveniently in very confined and difficult-to-access areas with enhanced hand clearance. The predefined locking positions at 0°, 15° und 90°, both to the right and left, ensure safe working without any slipping of the ratchet head. The ratchet can be used as a conventional screwdriver in the 0° position by attaching an adaptor and a bit. The flywheel design ensures rapid screwdriving. The rotation-symmetric construction of the Kraftform handle and the free-turning sleeve support rapid twisting. The outstanding design of the Kraftform handle fits perfectly into the hand preventing hand injuries such as blisters and calluses. The hard materials used for the handle ensure quick and easy hand repositioning without any danger of the skin "sticking" to the handle. The softer anti-slip zones enable the low-loss transfer of high torque. For 1/2" square sockets as well as 1/2" adaptors with square drive, equipped with ball lock. Including 17 Zyklop sockets, 2 Zyklop extensions with free-turning sleeve, 1 T-handle, 1 wobble extension, 1 adaptor with quick-release chuck, 13 bits. "Take it easy" Tool Finder with colour coding according to sizes.