

151-00982

# HellermannTyton



Article Number: 151-00982

Description: Heavy-Duty Metal Edge Clip, 1-3mm panel thickness, 5-7.6mm cable range, SS304, 100/bag

Base Data	Local Order Number	151-00982
	Type	MSC2
	Color	Metal (ML)
	Features and benefits	<ul style="list-style-type: none"> <li>• Integrated design allows for easy insertion by hand.</li> <li>• 1-3mm panel thickness range allows for multiple applications.</li> <li>• Double-compression design that accommodates various sizes of wire and cable.</li> <li>• Presents a high extraction force for withstanding extreme conditions.</li> </ul>
	Quantity Per	bag
	Product Description	HellermannTyton's Metal Edge Clip provides an excellent alternative to managing wire and PV cables where plastic fasteners are not the preferred method. Designed for effortless insertion, the Metal Edge Clip has a high extraction force that tolerates extreme environments and provides assurance that the cables are secure on a panel. The Metal Edge Clip is simple to install and can easily be removed with a flathead screwdriver.
	Short Description	Heavy-Duty Metal Edge Clip, 1-3mm panel thickness, 5-7.6mm cable range, SS304, 100/bag
	Product Dimensions	Length L (Imperial)
Length L (Metric)		24.0mm
Cable Diameter Max. (Imperial)		0.3"
Cable Diameter Max. (Metric)		7.6mm
Cable Diameter Min. (Imperial)		0.2"
Cable Diameter Min. (Metric)		5.0mm
Width W (Imperial)		0.5"
Width W (Metric)		13.0mm
Panel Thickness Max. (Imperial)		0.12"
Panel Thickness Max. (Metric)		3.0mm
Panel Thickness Min. (Imperial)		0.04"
Panel Thickness Min. (Metric)		1.0mm

151-00982



Material and Specifications		
	Material	Stainless Steel (SS304)
	Material Shortcut	SS304
	Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
	UL Listed (US)	Yes
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100Pieces
	Customs Number(Schedule B)	7326908595
	Content Unit (BMEcat)	pieces