

151-01664

HellermannTyton



Article Number: 151-01664

Description: Ratchet P-Clamp, 1.38"–2.01" Bundle Dia, 15° Short, .26" Hole Dia, PA66HIRHSUV/ST/ZN, Black, 160/ctn

| | | |
|--------------------|-------------------------------------|---|
| Base Data | | |
| | Local Order Number | 151-01664 |
| | Type | RCD15SM6 |
| | Color | Black (BK) |
| | Features and benefits | <ul style="list-style-type: none"> • One-piece ratchet closure design allows for easy installation during pre- or final assembly. • Four sizes and multiple configurations handle a wide range of diameters and applications, reducing part inventory. • Clamp interior is designed to guide and center bundle to reduce pinching. • Easy release feature allows for quick adjustments and maintenance. • Impact modified, heat and UV stabilized PA66 provides long-term durability, indoors and out. • Steel mounting plate tolerates high torque mounting and is treated to resist chemicals and salt spray. |
| | Quantity Per | carton |
| | Product Description | The Ratchet P-Clamp family offers versatility when managing wires, cables and hoses. The robust design and durable materials make it ideal for heavy duty applications, both indoors and out. The one-piece adjustable clamp can be closed by hand to the desired diameter. The release feature provides easy and nondestructive removal of cables simply by using a flat-head screwdriver. This nondestructive release allows the clamp to be reused without removing or replacing any bolts or screws. The Ratchet P-Clamp is offered in four sizes and multiple mounting configurations. |
| | Short Description | Ratchet P-Clamp, 1.38"–2.01" Bundle Dia, 15° Short, .26" Hole Dia, PA66HIRHSUV/ST/ZN, Black, 160/ctn |
| Product Dimensions | | |
| | Minimum Tensile Strength (Imperial) | 100.0lbs |
| | Minimum Tensile Strength (Metric) | 445.0N |
| | Length L (Imperial) | 7.12" |
| | Length L (Metric) | 180.9mm |
| | Length L2 (Imperial) | 4.56" |
| | Fixation Method | Screw Mounting |
| | Length L2 (Metric) | 115.9mm |
| | Variant | 15° Short |
| | Width W (Imperial) | 1.37" |

151-01664



| | | |
|-----------------------------|-------------------------------------|--|
| Product Dimensions | Width W (Metric) | 34.9mm |
| | Cable Tie Width Max. (Imperial) | 0.52" |
| | Cable Tie Width Max. (Metric) | 13.2mm |
| | Width W2 (Imperial) | 1.181" |
| | Width W2 (Metric) | 30.0mm |
| | Bundle Diameter Min. (Imperial) | 1.42" |
| | Bundle Diameter Min. (Metric) | 36.0mm |
| | Bundle Diameter Max. (Imperial) | 2.0" |
| | Bundle Diameter Max. (Metric) | 51.0mm |
| | Mounting Hole Diameter D (Imperial) | 0.256" |
| | Mounting Hole Diameter D (Metric) | M6 |
| | Mounting Hole Centers (Imperial) | 2.72" |
| | Stud Size (Metric) | M6 |
| | | |
| Material and Specifications | | |
| | Material | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| | Material Shortcut | ST |
| | Flammability | UL 94 HB |
| | Operating Temperature | -40°F to +257°F (-40°C to +125°C) |
| | ROHS Compliant | Yes |
| | Stamping Material | Steel (ST) |
| Logistic and Packaging | | |
| | Package Quantity (Imperial) | 160 |
| | Package Quantity (Metric) | 160 |
| | Customs Number(Schedule B) | 3926909987 |