

166-90251

Article Number: 166-90251

Description: HelaGuard SR PVC Tubing, Smooth Bore, Smooth Cover, Std Wt, 1.25" Dia, Bk, 100 ft/Std. Reel



| Base Data | |
|-------------------------------|--|
| Local Order Number | 166-90251 |
| Type | LPC1250 |
| Color | Black (BK) |
| Features and benefits | <ul style="list-style-type: none"> • Spiral reinforced construction provides protection from crushing yet remains extremely flexible. • Lightweight, easy-to-use material reduces installation time and labor costs. • Material stands up to vibration and limited torsional movement without creation of stress points or cracks. • Smooth inside bore protects wires and eases insertion of wire bundles. • UV resistant; suitable for use in outdoor applications. • Outer surface wipes clean in wash-down environments. |
| Quantity Per | reel |
| Product Description | A lightweight, smooth tubing made of a spiral reinforced PVC material that provides high flexibility; well-suited for protecting wire and cable bundles in extremely tight spaces. UV resistant. Use with HelaGuard Metallic or Non Metallic Compression (PSR) Fittings for IP67 rating. |
| Short Description | HelaGuard SR PVC Tubing, Smooth Bore, Smooth Cover, Std Wt, 1.25" Dia, Bk, 100 ft/Std. Reel |
| Product Dimensions | |
| Length L (Imperial) | 100.0ft |
| Length L (Metric) | 30.5m |
| Inner Diameter D (Imperial) | 1.39" |
| Inner Diameter D (metric) | 35.4mm |
| Trade Size | 1-1/4 " |
| Outside Diameter D (imperial) | 1.65" |
| Outside Diameter D (metric) | 41.8mm |
| Nominal Diameter (Imperial) | 1-1/4" |
| Nominal Diameter (Metric) | 40mm |
| Inside Bend Radius (Imperial) | 7.48" |
| Inside Bend Radius (Metric) | 190mm |

166-90251

| | | |
|-----------------------------|-----------------------------|--|
| Material and Specifications | | |
| | Material | Polyvinylchloride (PVC) |
| | Material Shortcut | PVC |
| | Flammability | self-extinguishing according to EN IEC 61386-1 |
| | Halogenfree | No |
| | Operating Temperature | +23°F to +158°F (-5°C to +70°C) |
| | ROHS Compliant | Yes |
| Logistic and Packaging | | |
| | Package Quantity (Imperial) | 100ft |
| | Package Quantity (Metric) | 30.5m |
| | Customs Number(Schedule B) | 3926909987 |