

166-90449

# HellermannTyton



Article Number: 166-90449

Description: HelaGuard Accessories, Sealing Washer, M32-1", Polyester Elastomer, Blue, 10/pkg

Base Data	
Local Order Number	RSW32-BU
Type	RSW100
Color	Blue (BU)
Features and benefits	<ul style="list-style-type: none"> <li>• Polyester elastomer washer provides ingress protection against moisture and is oil resistant.</li> <li>• Small "pips" in bore retain washer onto metric threaded fittings.</li> <li>• Ribs on both sides of washer enhances sealing performance.</li> </ul>
Quantity Per	pack
Product Description	Face sealing washer affixed between metric threaded fitting and entry wall surface to achieve IP66, IP67, IP68 and IP69 levels of ingress protection. Hardness 33 Shore D. Self-extinguishing and halogen free.
Technical Description	Manufacturer Reference Number: RSW32-BU
Short Description	HelaGuard Accessories, Sealing Washer, M32-1", Polyester Elastomer, Blue, 10/pkg
Product Dimensions	
Inner Diameter D (Imperial)	1.26"
Inner Diameter D (metric)	32.0mm
Outside Diameter D (imperial)	1.65"
Outside Diameter D (metric)	42.0mm
Nominal Diameter (Imperial)	1"
Nominal Diameter (Metric)	32.0mm
Thickness T (Imperial)	0.07"
Thickness T (Metric)	1.8mm
Material and Specifications	
Material	Thermoplastic Elastomer (TPE)
Material Shortcut	TPE
Operating Temperature	-58°F to +275°F (-50°C to +135°C)

166-90449



Logistic and Packaging		
	Package Quantity (Imperial)	10
	Package Quantity (Metric)	10Pieces
	Customs Number(Schedule B)	4016930000