

166-90097

HellermannTyton

Article Number: 166-90097



Description: HelaGuard Non-Metallic Fitting, IP66, 45-Elbow, 1.5" NPT Thread, 1.50" Dia, PA66, Black, 2/pkg

Base Data	
Local Order Number	166-90097
Type	HG150-45-1500
Color	Black (BK)
Features and benefits	<ul style="list-style-type: none"> • External NPT thread provides a secure connection. • Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits. • Elbow features a smooth, swept bore to ease cable installation. • All-around "teeth" attach firmly to conduit and deliver a high extraction force. • Durable nylon material has high resistance to salts, oils, weak acids and solvents. • IP66 fitting has one-piece construction. • IP68 fitting has additional conduit seal for increased protection against wind, dirt and water.
Quantity Per	bag
Product Description	Elbow fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. Choose from IP66 or IP68 ingress protection rated fittings.
Short Description	HelaGuard Non-Metallic Fitting, IP66, 45-Elbow, 1.5" NPT Thread, 1.50" Dia, PA66, Black, 2/pkg
Product Dimensions	
Length L (Imperial)	4.17"
Length L (Metric)	106mm
Bore Diameter (Imperial)	1.54"
Bore Diameter (Metric)	39.0mm
Clearance Hole Diameter (Imperial)	1.882"
Clearance Hole Diameter (Metric)	47.8mm
Euro (NW) Size	48mm
Swivel Thread (Y/N)	No
Thread Length (Imperial)	0.63"
Thread Type	NPT
Trade Size	1-1/2 "

166-90097



Product Dimensions	Variant	45° Elbow
	Outside Diameter D (imperial)	2.99"
	Outside Diameter D (metric)	76.0mm
	Nominal Diameter (Imperial)	1-1/2"
	Nominal Diameter (Metric)	54mm
	Thread Length (metric)	16mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
	ROHS Compliant	Yes
	UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes	
Logistic and Packaging		
	Package Quantity (Imperial)	2
	Package Quantity (Metric)	2Pieces
	Customs Number(Schedule B)	3926909987