

166-90135

HellermannTyton

Article Number: 166-90135



Description: HelaGuard Non-Metallic IP65 Fitting, Straight, NPT Thread, 0.75" Dia, PA66, Black, 10/pkg

Base Data		
	Local Order Number	166-90135
	Type	PSR075-S-0750
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • External NPT thread provides a secure connection. • Twist-on installation makes future access fast and easy. • Internal spigot design helps ease threading of fitting onto conduit. • All-around "teeth" attach firmly to conduit and deliver a high extraction force. • Durable nylon material has high resistance to salts, oils, weak acids and solvents. • IP65 rating for protection against wind, dirt and low pressure jets of water from all directions.
	Quantity Per	bag
	Product Description	Compression fittings feature a twist-on design for easy installation and future access. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Fits HelaGuard non-metallic conduits and tubing.
	Short Description	HelaGuard Non-Metallic IP65 Fitting, Straight, NPT Thread, 0.75" Dia, PA66, Black, 10/pkg
Product Dimensions		
	Length L (Imperial)	1.77"
	Length L (Metric)	45mm
	Bore Diameter (Imperial)	0.75"
	Bore Diameter (Metric)	19.0mm
	Clearance Hole Diameter (Imperial)	1.039"
	Clearance Hole Diameter (Metric)	26.4mm
	Thread Length (Imperial)	0.59"
	Trade Size	3/4 "
	Outside Diameter D (imperial)	1.65"
	Outside Diameter D (metric)	42mm
	Nominal Diameter (Imperial)	3/4"
	Nominal Diameter (Metric)	25mm
	Thread Length (metric)	15mm

166-90135



Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +248°F (-40°C to +120°C)
	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	10
	Package Quantity (Metric)	10Pieces
	Customs Number(Schedule B)	3926909987