

166-90107

HellermannTyton

Article Number: 166-90107



Description: HelaGuard Non-Metallic IP66 Fitting, Straight, NPT Thread, 1.25" Dia, PA66, Black, 2/pkg

Base Data		
	Local Order Number	166-90107
	Type	HG125-S-1250
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • External NPT thread provides a secure connection. • Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits. • All-around "teeth" attach firmly to conduit and deliver a high extraction force. • Durable nylon material has high resistance to salts, oils, weak acids and solvents. • IP66 fitting has one-piece construction. • IP68 fitting has additional conduit seal for increased protection against wind, dirt and water.
	Quantity Per	bag
	Product Description	Straight fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. Choose from IP66 or IP68 ingress protection rated fittings.
	Short Description	HelaGuard Non-Metallic IP66 Fitting, Straight, NPT Thread, 1.25" Dia, PA66, Black, 2/pkg
Product Dimensions		
	Length L (Imperial)	2.36"
	Length L (Metric)	60mm
	Bore Diameter (Imperial)	1.28"
	Bore Diameter (Metric)	32.5mm
	Clearance Hole Diameter (Imperial)	1.649"
	Clearance Hole Diameter (Metric)	41.9mm
	Euro (NW) Size	36mm
	Swivel Thread (Y/N)	No
	Thread Length (Imperial)	0.63"
	Thread Type	NPT
	Trade Size	1-1/4 "
	Variant	Straight

166-90107

HellermannTyton

Product Dimensions	Outside Diameter D (imperial)	2.48"
	Outside Diameter D (metric)	63mm
	Nominal Diameter (Imperial)	1-1/4"
	Nominal Diameter (Metric)	42mm
	Thread Length (metric)	16mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	2
	Package Quantity (Metric)	2Pieces
	Customs Number(Schedule B)	3926909987