



#### RE660-LF

- Epoxy glass hard fabric FR4 1.50 mm
- Two-sided 35  $\mu$ m Cu
- Plated-through (PTH)
- Hot tinned (HAL lead free)
- Two raster fields with 7 x 37 soldering pads each (1.70 x 1.70 mm) in raster 2.54 mm (bore  $\varnothing$  1.10 mm)
- 21 soldering pads (1.70 x 1.70 mm) in raster 7.50 mm (bore  $\varnothing$  1.10 mm)
- 21 three hole pads in raster 7.50 mm, which are transferred to a raster 2.54 mm
- 21 soldering pads (1.70 x 1.70 mm) in raster 7.62 mm (bore  $\varnothing$  1.10 mm)
- 21 three hole pads in raster 7.62 mm, which are transferred to a raster 2.54 mm
- Pre-scored predetermined breaking point
- Size 100 x 160 mm