

USB Type C Charger

Rated to 60 Watts (with Power Delivery (PD) feature)

Features:

- 1 x USB type C port rated to 3A (60 Watt maximum)
- The 3 Amp output on the Type C port provides fast efficient charging
- 4 stage USB Power Delivery (USB-PD) **5V / 9V / 12V / 20V with auto detection**
- 3 x USB type A ports rated to 2.4A (12 Watt maximum)
- Total 72 Watts maximum combined output rating
- Compatible with all USB type C enabled devices & wide range of other USB devices
- 2 pin Fig.8 input & wide range input voltage for World use (100-240vac)
- Over charging protection –auto stop when battery full
- Integrated intelligent IC to detect connected devices charging requirement
- Over current, short circuit and over temperature protection
- Suitable for use with both Macbook and Chromebook as well as comprehensive range of smartphones and gaming devices
- UK mains lead included
- CE and UL safety approved
- Charge multiple devices at the same time from the 4 x USB ports



Part number	Output 1 (Type C)	Output 2	Output 3	Output 4
USB-C-72W	5V / 9V / 12V / 20V @ 3A max	5vdc 2.4A max	5vdc @ 2.4A max	5vdc @ 2.4A max

The Maximum output from the USB Type C port is 60W. The maximum output from all 4 ports is 72 Watts



Please refer to the photo to the left which shows the input of the fast charger. It has an industry standard 2 pin Figure 8 input with a wide range 100-240vac input voltage so can be used anywhere in the world. Just switch the mains lead.

A UK power cord is included as standard



The USB Type C connector can be plugged in either way round like the Apple lightning connector

