

# TY125-18-100



Products Low Voltage Products and Systems Installation Products Wire Management and Connectivity Cable Ties

## General Information

<b>Extended Product Type:</b>	TY125-18-100
<b>Product ID:</b>	7TCG054360R0106
<b>EAN:</b>	5414363060420
<b>Catalog Description:</b>	CBL TIE 18LB 5IN NATURAL NYLON
<b>Long Description:</b>	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 142mm (5.59 Inches), Width of 2.5mm (0.10 Inches), Thickness of 1.2mm (0.05 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), 100 Pack

## Additional Information

<b>Brand / Label:</b>	TY-FAST
<b>Country of Origin:</b>	Hungary (HU)
<b>Customs Tariff Number:</b>	3926909996
<b>Data Sheet, Technical Information:</b>	TY125-18-100
<b>E-nummer:</b>	1519704
<b>EAN:</b>	5414363060420
<b>ETIM 6:</b>	EC000046 - Cable tie
<b>Instructions and Manuals:</b>	TY125-18-100
<b>Invoice Description:</b>	CBL TIE 18LB 5IN NATURAL NYLON
<b>Minimum Order Quantity:</b>	100 piece
<b>Package Level 1 EAN:</b>	00786210288130
<b>Package Level 1 Height:</b>	152.4 mm
<b>Package Level 1 Length:</b>	254 mm
<b>Package Level 1 Units:</b>	100 piece
<b>Package Level 1 Width:</b>	25.4 mm
<b>Package Level 2 EAN:</b>	50786210288135
<b>Package Level 2 Height:</b>	165.1 mm
<b>Package Level 2 Length:</b>	215.9 mm
<b>Package Level 2 Units:</b>	1000 piece
<b>Package Level 2 Width:</b>	175.26 mm
<b>Product Main Type:</b>	CABLE TIES AND ACCESSORIES
<b>Product Name:</b>	NYLON CABLE TIE
<b>Product Net Weight:</b>	0.286 g
<b>Selling Unit of Measure:</b>	each
<b>UNSPSC:</b>	39121703
<b>UPC:</b>	786210288130

