

Erem 5" Oval Head Semi-Flush Cutter, Ergonomic Handles



◀◀ previous print close next ▶▶

Product Details

Catalog No.	2412E
UPC Code	4003019099740
Length (Inches)	5.00
Head Style/Cut Type	Oval/Semi-Flush
Max Cutting Diameter (Inches)	.050
Jaw Length (Inches)	.453
Head Width (Inches)	.453
Head Thickness (Inches)	.380
Application	General Use
Packaging	Industrial Box/Carton
Low Res. Image	2412E_100.jpg
High Res. Image	2412E_300.jpg
Stock Item	Normal Stock Item

Package Details (Dimensions)

[Email this Page](#)

Product Features:

- Co-molded ergo grip for maximum comfort
- Oval head diagonal cutter
- Semi-flush cut
- For soft copper wire 32-16 AWG
- Made of extruded 100% machined Eremadium® tool steel for durability
- Patent internal Magic® spring maintains constant Fatigue-free operation
- Erem Maximum Opening Stop (EMOS) limits handles from opening