

### FEATURES:

- Interchangeable tips are securely held in a friction socket
- Stainless steel tips are best for penetrating coatings or contaminants
- For precise measurements, use Gold-plated tips. See model 6354
- IEC 1010 compliant, CAT III, 1000 V, 3 Amperes
- Right angle sheathed banana plug for use with hand held digital multimeters.

### MATERIALS:

Probe Body: Outer Insulation - Santoprene® Rubber, Color: Gray  
Inner Insulation – Polypropylene

Right Angle Sheathed Banana Plug:

Plug Body: Nickel plated brass.

Banana Plug Spring: Nickel plated Beryllium-Copper.

Insulation: Polypropylene

Wire: 20 AWG silicon rubber .089 (2,26mm) O.D.

Color: Gray

Tips: Stainless steel.

### RATINGS:

Operating Voltage: 1000 Max.

Current: 3 Amperes

### ORDERING INFORMATION: Model 6275

One red probe, one black probe with stainless steel tips.

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.  
Registered trademarks are the property of their respective companies. Made in USA