

Erem Cutter, Pneumatic, Diagonal Round Head, Full Flush Cut



◀◀ previous print close next ▶▶

Product Details

Catalog No.	1522N
UPC Code	037103204462
Length (Inches)	1.80
Head Style/Cut Type	Tapered/Full Flush
Pressure (PSI)	N/A
Max Cutting Diameter (Inches)	.063
Jaw Length (Inches)	.394
Head Width (Inches)	.413
Head Thickness (Inches)	.256
Packaging	Industrial Box/Carton
Low Res. Image	1522N_100.jpg
High Res. Image	1522N_300.jpg
Stock Item	Normal Stock Item

Package Details (Dimensions)

Email this Page

Product Features:

- **Diagonal round head**
- **For medium hard wire**
- **Full flush cut**
- **Rated at over 1 million cuts**