

THB.381.A2A

Micro Plug 2 pole Screw terminal 5.8mm to 6.9mm cable diameter, IP68 10A 400V 1 cable entry



SPECIFICATION

Type	Plug
Cable Entries	1
Number of Poles	2
Terminal Type	Silver-plated brass (zinc-plated screws)
Body Material	PA66 GF UL94 V0
IP Rating	68
Max Current (A)	10
Max Voltage (V)	400
Minimum Temp Rating °C	-40
Max Temp Rating °C	125
Minimum Cable Diameter (mm)	5.8
Maximum Cable Diameter (mm)	6.9
Fixing System	Cable
Temperature "T" Rating	T125