



Main

Product or component type	Starter
Range of product	S
Line Rated Current	9 A
Product certifications	CSA NEMA UL listed
Control circuit	Separate control circuit
Control type	No control units
NEMA degree of protection	Not rated (open device)
Rated power in HP	0.33 HP 115 V AC 1 HP 230 V AC
Poles description	2P
Phase	1 phase
System Voltage	600 V AC
NEMA size	00
Control circuit voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Electrical connection	Screw clamp terminals
Thermal overload type	Melting alloy 1

Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
GTIN	00785901608387
Nbr. of units in pkg.	1
Package weight(Lbs)	3.8900000000000001
Returnability	N

Country of origin	MX
-------------------	----

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
