

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022013057

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 254 Crimp Housing, Friction Ramp, 5 Circuits

Documents:

3D Model

Packaging Specification PK-2695-001-001 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification PS-10-07-001 (PDF)

|                               |                                 |
|-------------------------------|---------------------------------|
| Agency Certification          |                                 |
| CSA                           | LR19980                         |
| UL                            | E29179                          |
| General                       |                                 |
| Product Family                | Crimp Housings                  |
| Series                        | 2695                            |
| Application                   | Signal, Wire-to-Board           |
| Overview                      | KK® Interconnect System - Molex |
| Product Name                  | KK® 254                         |
| UPC                           | 800753593855                    |
| Physical                      |                                 |
| Circuits (maximum)            | 5                               |
| Color - Resin                 | Natural (White)                 |
| Flammability                  | 94V-0                           |
| Gender                        | Receptacle                      |
| Glow-Wire Compliant           | No                              |
| Lock to Mating Part           | Yes                             |
| Material - Resin              | Nylon                           |
| Net Weight                    | 0.520/g                         |
| Number of Rows                | 1                               |
| Packaging Type                | Bag                             |
| Panel Mount                   | No                              |
| Pitch - Mating Interface      | 2.54mm                          |
| Pitch - Termination Interface | 2.54mm                          |
| Polarized to Mating Part      | Yes                             |
| Stackable                     | No                              |
| Temperature Range - Operating | See Product Specification       |
| Solder Process Data           |                                 |
| Lead-freeProcess Capability   | N/A                             |
| Material Info                 |                                 |
| Engineering Number            | 2695-05RP                       |
| Reference - Drawing Numbers   |                                 |
| Packaging Specification       | PK-2695-001-001                 |
| Product Specification         | PS-10-07-001                    |
| Sales Drawing                 | SD-2695                         |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per

-ED/01/2017 (12

January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product

environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

2695 Series

Mates With

KK®254 PCB Headers [42375](#) , [42377](#)

, [42376](#) , [4030](#) , [6373](#) , [6410](#) , [171856](#) ,

[171857](#)

Use With

[2759](#) , [4809](#) KK® Crimp terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION