

# Electronic housing - UCS 125-87-H-GD 7035 - 2203331

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Complete housing for PCBs, can be positioned flexibly; includes housing half shells, side panels closed, adhesive domes for PCB attachment, screws for housing and PCB attachment; light gray housing with turquoise-green corner inlays

## Why buy this product

- High degree of application flexibility, thanks to the modular housing design
- Flexible PCB attachment, adapts to virtually all form factors
- Practical customization options
- Reduced logistics outlay, thanks to components which are compatible with one another



## Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 404431
GTIN	4055626404431
Weight per Piece (excluding packing)	174.880 g
Custom tariff number	39269097
Country of origin	Germany
Note	Made to Order (non-returnable)

## Technical data

### General

Housing type	Complete housing
Housing material	PC
Color (RAL)	gray (7035)

### Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 100 °C (depending on power dissipation)

# Electronic housing - UCS 125-87-H-GD 7035 - 2203331

## Technical data

### Dimensions

Width	125 mm
Height	87 mm
Depth	67 mm

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

## Classifications

### eCl@ss

eCl@ss 5.1	27180506
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

### ETIM

ETIM 5.0	EC001031
----------	----------

## Accessories

### Accessories

#### Screwdriver tools

Screwdriver - SF-TXH 10X80 - 1200149



Screwdriver, Torx® with bore hole, TX 10 x 80, two-component handle