



### FEATURES:

Model 6475 is a set of two each of the following five probes that fit Pomona probes that use the .054Ø test probe tips. Individual replacement probe tips are available in packages of 10.

#### Model 6221 Sharp Stainless-Steel Tip

- Rigid stainless-steel tip is hardened for heavy duty use
- Sharp, hardened point will penetrate conformal coatings and heavy surface contamination

#### Model 6222 Nickel Plated Brass Tip

- Rigid nickel plated brass tip is perfect for precision measurement
- Sharp tip resists wear
- This is the best tip for every day use

#### Model 6219 Triple Point Micro Tip

- Gold plated pogo pin tip has .018" diameter Tip with three sharp points
- Sharp point digs into soft metals like solder for low resistance connections
- Self-cleaning tip pierces surface coatings or contamination
- Pogo pin helps to hold the test point even if the probe is moved

#### Model 6218 Sharp Point Tip

- Gold plated pogo pin tip has a sharp tapered point
- Sharp point digs into soft metals like solder for low resistance connections
- Self-cleaning tip pierces surface coatings or contamination
- Pogo pin helps to hold the test point even if the probe is moved

#### Model 6220 Triple Point Tip

- Gold plated pogo pin tip has three sharp points
- Sharp point digs into soft metals like solder for low resistance connections
- Self-cleaning tip pierces surface coatings or contamination
- Pogo pin helps to hold the test point even if the probe is moved

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360  
Technical Assistance: 800-241-2060

PomonaACCESS 90888 (800) 444-6785 or (425) 446-6010  
More drawings available at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

Probe Tip Description	Part Number	Body Dia.	Tip Dia.	Kit Quantity
Sharp Stainless Steel Tip	6221	.054"	.054"	2
Nickel Plated Brass Tip	6222	.054"	.054"	2
Triple Point, Micro Pogo-Pin Tip	6219	.054"	.018"	2
Sharp Point Pogo-Pin Tip	6218	.054"	.040"	2
Triple Point Pogo-Pin Tip	6220	.054"	.040"	2

**MATERIALS:**

Pogo-pin Tips: Gold Plated Beryllium Copper

Rigid Tips: Model 6221: Stainless-Steel, Model 6222: Nickel Plated Brass

**RATINGS:**

Maximum Current: 5 Amperes

**ORDERING INFORMATION:** Full Kit: Model 6475

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.  
Registered trademarks are the property of their respective companies. Made in USA