BMP®41 Label Printer

BradyID.com/bmp41





Online Video!

Visit BradylD.com/bmp41 for more information or to view an online printer demo video.

Your Complete Printing Solution:

BMP41 cartridges with label and print ribbon.....page 298

BMP®41 Label Printer & Accessories

Catalog #	Description
BMP41	BMP41 Label Printer with Hard Case*
BMP41-KIT-VD	BMP41 Printer DataComm Starter Kit*
BMP41-KIT-EL	BMP41 Printer Electrical Starter Kit*
BMP41-KIT-GI	BMP41 Printer Facility ID Starter Kit*
BMP41-BATT	BMP41 Rechargeable Battery Pack
BMP41-QC	BMP41 External Battery Quick Charger
BMP41-AC	BMP41 AC Adapter / Battery Charger
BMP41-MAGNET	BMP41 Magnet Accessory
BMP41-HC	BMP41 Hard Case
BMP41-USB	BMP41 USB Cable

*Printer ships with BMP41 printer, NiMH battery, AC adapter / charger, hard case, MC1-1000-595-WT-BK cartridge, USB cable, product & drivers CD, and quick start quide

BMP°41 LABEL PRINTER

ONE AND DONE. BMP®41 Printer Does It All!

A rugged, handheld labeling solution that gives you the versatility of die-cut labels and continuous labels in one printer!


- Quick-load, drop-in cartridges for quick supply change and automatic label formatting
- Fast print speed of 1.3" per second
- Over 100 label parts in 11 materials
- 3/4" sleeves and 1" wide continuous output
- Drop tested rugged industrial bumpers with a grab and go grip to be on the move with you
- Large graphical LCD display with backlight to see exactly what you're printing
- Rechargeable NiMH battery, AA or AC adapter, for long lasting power supply
- Built-in wizard-style apps for wire ID, cabel flags, terminal blocks, patch panels, breaker boxes and general ID





BMP®41 Printer S	nonifications
Max Labels Per	precincations
Day	Average 250 labels/day
Print Resolution	300 dpi
Print Technology	Thermal transfer
Print Speed	133mm/sec (1.3in/sec)
Tape Widths	Various sizes from
(inches)	0.235" to 1.0"
Tape Widths	Various sizes from
(mm)	5.969 mm to 25.4 mm
Max Label Width	1.00" (25.4mm)
Max Print Width	0.96" (24.4 mm)
Memory	48 MB / Up to 25,000
	Labels
Materials	M-, MC-, MC1- Series Cartridges (1.00" and 0.75"
Supported	height only)
ouppo.tou	100+ Stock Parts
Continuous vs	Continuous and die cut
Die Cut Labels	labels
Connectivity	Yes
Options	LICD
PC Connectivity	USB
Software Compatibility	Optional through USB
File Transfer from	Yes - with Labelmark®
PC to printer	Software
Wireless	No
Connectivity	INO
Stand Alone	Yes
Printing	
Color Capability	Single print color on a label
Keyboard	QWERTY
Backlit Screen	2.5" x 1.4", user adjustable backlit
Text Sizes	4 to 103pt + autosizing
Multi-Line Print	Yes
Print Rotation	Yes
Serialization	Yes
Barcode	39 and 128
Symbols	
Categories	450
Portability	Yes
ĺ	Adhesive Polyester,
	PermaSleeve® Heat Shrink
1 -1-17	Tubing, Polypropylene
Label Types or Application	Tags, Self-laminating Vinyl, Metallized Polyester Ultra
Functions	Aggressive Polyester,
	Repositional Vinnl Cloth,
	Nylon Cloth, Reflective
	Tape, Indoor/Outdoor Vinyl,
	Basic and Die Cut labels
	for Wire and Cable ID, Datacomm and AV
Applications	labeling, Electrical ID, Panel
pp	ID, Product ID, Facility ID,
	Safety and Maintenance,
	General ID
Power Supply	AC Power, rechargable
	DAIRING DAIRIN

Exceptional material variety and durability.





Labelina







Weight

Warranty



NiMH battery

2 years

2.6 lbs (1.2 kg)

Voice & Data Communications

PermaSleeve® Wire Marking

Indoor / Outdoor Vinyl Labels...and more!

