

# BMP®51 and BMP®53 Materials

BradyID.com/bmp51

## Indoor / Outdoor Vinyl Material (B-595)

Pliable vinyl with highly aggressive adhesive conforms well to smooth or rough surfaces such as pipes, panels, shelving, bins, and equipment. Ideal for production ID and lean 5S labeling. Excellent resistance to oils, detergents, dirt, grime, and many solvents. Label last up to 8-10 years outdoors.



Figure 33



Portable Printers

Fits Printer Model	Diagram	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Roll Length B Inch (mm)	Labels/Roll
<b>B-595 – Indoor / Outdoor Vinyl Tape</b>								
BMP41, 51, 53	Fig. 33	MC-500-595-WT-BK	B-595	Vinyl	BK on WT	0.500 (12.70)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-750-595-WT-BK	B-595	Vinyl	BK on WT	0.750 (19.10)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC1-1000-595-WT-BK	B-595	Vinyl	BK on WT	1.000 (25.40)	25 ft. (7.62 m)	1 roll (cont.)
BMP51, 53	Fig. 33	MC-1500-595-WT-BK	B-595	Vinyl	BK on WT	1.500 (38.10)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-500-595-YL-BK	B-595	Vinyl	BK on YL	0.500 (12.70)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-750-595-YL-BK	B-595	Vinyl	BK on YL	0.750 (19.10)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC1-1000-595-YL-BK	B-595	Vinyl	BK on YL	1.000 (25.40)	25 ft. (7.62 m)	1 roll (cont.)
BMP51, 53	Fig. 33	MC-1500-595-YL-BK	B-595	Vinyl	BK on YL	1.500 (38.10)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-500-595-OR-BK	B-595	Vinyl	BK on OR	0.500 (12.70)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-750-595-OR-BK	B-595	Vinyl	BK on OR	0.750 (19.10)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC1-1000-595-OR-BK	B-595	Vinyl	BK on OR	1.000 (25.40)	25 ft. (7.62 m)	1 roll (cont.)
BMP51, 53	Fig. 33	MC-1500-595-OR-BK	B-595	Vinyl	BK on OR	1.500 (38.10)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-500-595-BL-WT	B-595	Vinyl	WT on BL	0.500 (12.70)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-750-595-BL-WT	B-595	Vinyl	WT on BL	0.750 (19.10)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC1-1000-595-BL-WT	B-595	Vinyl	WT on BL	1.000 (25.40)	25 ft. (7.62 m)	1 roll (cont.)
BMP51, 53	Fig. 33	MC-1500-595-BL-WT	B-595	Vinyl	WT on BL	1.500 (38.10)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-500-595-RD-WT	B-595	Vinyl	WT on RD	0.500 (12.70)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-750-595-RD-WT	B-595	Vinyl	WT on RD	0.750 (19.10)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC1-1000-595-RD-WT	B-595	Vinyl	WT on RD	1.000 (25.40)	25 ft. (7.62 m)	1 roll (cont.)
BMP51, 53	Fig. 33	MC-1500-595-RD-WT	B-595	Vinyl	WT on RD	1.500 (38.10)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-500-595-GN-WT	B-595	Vinyl	WT on GN	0.500 (12.70)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-750-595-GN-WT	B-595	Vinyl	WT on GN	0.750 (19.10)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC1-1000-595-GN-WT	B-595	Vinyl	WT on GN	1.000 (25.40)	25 ft. (7.62 m)	1 roll (cont.)
BMP51, 53	Fig. 33	MC-1500-595-GN-WT	B-595	Vinyl	WT on GN	1.500 (38.10)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-500-595-WT-RD	B-595	Vinyl	RD on WT	0.500 (12.70)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-750-595-WT-RD	B-595	Vinyl	RD on WT	0.750 (19.10)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC1-1000-595-WT-RD	B-595	Vinyl	RD on WT	1.000 (25.40)	25 ft. (7.62 m)	1 roll (cont.)
BMP51, 53	Fig. 33	MC-1500-595-WT-RD	B-595	Vinyl	RD on WT	1.500 (38.10)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-500-595-BK-WT	B-595	Vinyl	WT on BK	0.500 (12.70)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-750-595-BK-WT	B-595	Vinyl	WT on BK	0.750 (19.10)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC1-1000-595-BK-WT	B-595	Vinyl	WT on BK	1.000 (25.40)	25 ft. (7.62 m)	1 roll (cont.)
BMP51, 53	Fig. 33	MC-1500-595-BK-WT	B-595	Vinyl	WT on BK	1.500 (38.10)	25 ft. (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-500-595-CL-BK	B-595	Vinyl	BK on CL	0.500 (12.70)	20 ft. (6.09 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-750-595-CL-BK	B-595	Vinyl	BK on CL	0.750 (19.10)	20 ft. (6.09 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC1-1000-595-CL-BK	B-595	Vinyl	BK on CL	1.000 (25.40)	20 ft. (6.09 m)	1 roll (cont.)
BMP51, 53	Fig. 33	MC-1500-595-CL-BK	B-595	Vinyl	BK on CL	1.500 (38.10)	20 ft. (6.09 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-500-595-CL-WT	B-595	Vinyl	WT on CL	0.500 (12.70)	20 ft. (6.09 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-750-595-CL-WT	B-595	Vinyl	WT on CL	0.750 (19.10)	20 ft. (6.09 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC1-1000-595-CL-WT	B-595	Vinyl	WT on CL	1.000 (25.40)	20 ft. (6.09 m)	1 roll (cont.)
BMP51, 53	Fig. 33	MC-1500-595-CL-WT	B-595	Vinyl	WT on CL	1.500 (38.10)	20 ft. (6.09 m)	1 roll (cont.)

## Reflective Material (B-584)

- Highly reflective material shines back brightly when struck by light
- Ideal for labeling outdoor utility poles and pedestals, hard hats, jobsite equipment and roof-top equipment
- Recommended for low light or inclement weather conditions




Figure 33



Fits Printer Model	Diagram	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Roll Length B Inch (mm)	Labels/Roll
<b>B-584 – Reflective Tape</b>								
BMP41, 51, 53	Fig.33	MC-500-584	B-584	Reflective Tape	BK on WT	0.500 (12.70)	20 ft. (6.09 m)	1 roll (cont.)
BMP41, 51, 53	Fig.33	MC-750-584	B-584	Reflective Tape	BK on WT	0.750 (19.05)	20 ft. (6.09 m)	1 roll (cont.)
BMP41, 51, 53	Fig.33	MC-1000-584	B-584	Reflective Tape	BK on WT	1.000 (25.40)	20 ft. (6.09 m)	1 roll (cont.)
BMP51, 53	Fig.33	MC-1500-584	B-584	Reflective Tape	BK on WT	1.500 (38.10)	20 ft. (6.09 m)	1 roll (cont.)
BMP41, 51, 53	Fig.33	MC-500-584-YL	B-584	Reflective Tape	BK on YL	0.500 (12.70)	20 ft. (6.09 m)	1 roll (cont.)
BMP41, 51, 53	Fig.33	MC-750-584-YL	B-584	Reflective Tape	BK on YL	0.750 (19.05)	20 ft. (6.09 m)	1 roll (cont.)
BMP41, 51, 53	Fig.33	MC-1000-584-YL	B-584	Reflective Tape	BK on YL	1.000 (25.40)	20 ft. (6.09 m)	1 roll (cont.)
BMP51, 53	Fig.33	MC-1500-584-YL	B-584	Reflective Tape	BK on YL	1.500 (38.10)	20 ft. (6.09 m)	1 roll (cont.)