



Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch head
Device short name	ZC2J
Head type	Rotary head
Product compatibility	XC2J
Associated lever	ZC2JY11 ZC2JY12 ZC2JY13 ZC2JY31 ZC2JY51 ZC2JY81 ZC2JY91
Associated body	ZC2JC4 ZC2JC48 ZC2JD4
Movement of operating head	Rotary
Type of operator	Without operating lever spring return
Type of approach	Lateral approach 2 directions

Complementary

Switch actuation	From left and right CW and CCW
Positive opening	Without
Product weight	0.21 kg
Head material	Metal

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0953 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.