



CABLE TYPES					
	RG-58C/U (Black)	RG-59B-U (Black)	RG-174/U (Black)	RG-62A/U (Black)	RG-223/U (Black)
	2249-C-XX	2249-E-XX	2249-K-XX	2249-M-XX	2249-Y-XX
Cap. pF./ft.	30.8	20.5	30.8	13.5	30.8
Nom.Imp.Ohms	50	75	50	93	50
Length in Inches	12,24,36,48,60, 72,120,180	12,24,36,48,60, 72,300,600	12,24,36,48,60, 300,360,600	12,24,36,48,60, 96,300,360,600	6,12,24,36,48,60, 72,96,120,144,180, 240,300,360,600

FEATURES:

- Assorted cables offered: See table above.

MATERIALS:

Connectors: BNC Male

Body: Brass, Tarnish resistant plating

Dielectric: PTFE

Center Contact – Gold Plated Brass

Strain Relief: PVC molded directly to cable and connectors

Marking: “Pomona 2249-X-XX”

RATINGS:

Operating Voltage: Shield/Earth: 30VAC/60VDC Max.

Inner Conductor/Shield: 500VRMS Max.

Operating Temperature: +50°C (+122°F) Max.

ORDERING INFORMATION: Model 2249-X-XX

X = Cable Type, see table above

XX = Cable Lengths, Standard Lengths: 6” (152,4), 12” (305), 24” (610), 36” (914), 48” (1219), 60” (1524), 72” (1829), 96” (2438,4), 120” (3048), 144” (3657,6), 180” (4572), 240” (6096), 300” (7620), 360” (9144) & 600” (15240).

Additional lengths can be quoted upon request.

Ordering Example: 2249-C-72 Indicates 72” in length.

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90134 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com