


KEMET Part Number: FC0H224ZFTBR24
(USCFC00H224ZBC)

Supercapacitors, SMD Can, Commercial Grade, FC, 0.22 F, -20/+80%, 5.5 V, V-Chip



Dimensions

D	10.5mm +/-0.5mm
L	8.5mm MAX
W	10.8mm +/-0.2mm
S	5mm NOM
G	0mm +0.3/-0.1mm

Packaging Specifications

Lead:	V-Chip
Packaging:	T&R, 380mm

General Information

Series:	FC
Description:	Surface Mount Double Layer Capacitor
Features:	Ultra Low ESR, High Power Pulse
RoHS:	Yes

Specifications

Capacitance:	0.22 F
Capacitance Tolerance:	-20/+80%
Voltage DC:	5.5 VDC, 4.2 VDC (Holding Voltage)
Temperature Range:	-25/+70C
Rated Temperature:	70C
Resistance:	25000 mOhms (1kHz)
Current:	0.33 mAmps (30min)