


Film, Metallized Paper, Resistor/Capacitor, P409, 0.47 uF, 20%, 630 V, 85C, Lead Spacing = 25.4mm



General Information	
Dielectric:	Metallized Paper
Style:	Radial
Series:	P409
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Approvals:	ENEC, UL, cUL
Construction:	Molded
Miscellaneous:	Resistor Tolerance: +/-30%. Resistor= 220 Ohms

Dimensions	
L	30.5mm MAX
H	22mm MAX
T	15.3mm MAX
S	25.4mm +/-0.4mm
LL	30mm +5mm
F	1mm +/-0.05mm

Specifications	
Capacitance:	0.47 uF
Capacitance Tolerance:	20%
Voltage DC:	630 VDC
Voltage AC:	275 VAC
Temperature Range:	-40/+85C
Rated Temperature:	85C
Insulation Resistance:	2.128 GOhms
Safety Class:	X2

Packaging Specifications	
Packaging:	Bulk
Packaging Quantity:	75