


Film, Metallized Polypropylene, Commercial Grade, R75, 10 uF, 5%, 400 V, 85C, Lead Spacing = 37.5mm



Dimensions

L	41.5mm +0.3mm
H	44mm +0.1mm
T	24mm +0.3mm
S	37.5mm +/-0.4mm
LL	30mm +5mm
F	1mm +/-0.05mm

Packaging Specifications

Packaging:	Bulk
Packaging Quantity:	72

General Information

Dielectric:	Metallized Polypropylene
Style:	Radial
Series:	R75
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
AEC-Q200:	Yes

Specifications

Capacitance:	10 uF
Capacitance Tolerance:	5%
Voltage DC:	400 VDC
Voltage AC:	220 VAC
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	0.1% 1kHz
Insulation Resistance:	3 GOhms
Max dVdt:	70 V
Inductance:	20 nH