
## **KEMET Part Number: SC-02-100**

(UALSC021000000)



## Choke, SC, 1000 uH



General Information		
Through-Hole Toroid		
SC		
Standard Common Mode Filter		
Yes		
Inductance Measurement Condition: 100kHz 1mA KC547		
Lead Spacing (S/S1) Are For Reference Only.		

Dimensions		
L	23mm MAX	
Т	18.5mm MAX	
Н	23mm MAX	
S	17mm MAX	
S1	6mm NOM	
LL	15mm +/-2mm	
Wire Size	0.6mm	

Specifications		
Inductance:	1000 uH	
Rated Temperature:	105C	
Current:	2 Amps	
Voltage AC:	250 VAC	
DC Resistance:	100 mOhms	
Insulation Resistance:	100 MOhms	

Packaging Specifications	
Weight:	15 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

