
KEMET Part Number: SC-10-20JH

(UALSC1020JH000)



Choke, SC-JH, 2000 uH



Dimensions		
L	42mm MAX	
Т	41mm MAX	
Н	30mm MAX	
S	30mm MAX	
S1	17mm NOM	
LL	5mm +/-2mm	
Wire Size	1.4mm	

Packaging Specifications		
Weight:	72 g	

General Information		
Style:	Through-Hole Toroid	
Series:	SC-JH	
Description:	Common Mode Filter With Base Plate	
RoHS:	Yes	
Miscellaneous:	Inductance Measurement Condition: 100kHz 1mA KC547	
Notes:	Lead Spacing (S/S1) Are For Reference Only.	

Specifications		
Inductance:	2000 uH	
Rated Temperature:	105C	
Current:	10 Amps	
Voltage AC:	250 VAC	
DC Resistance:	22 mOhms	
Insulation Resistance:	100 MOhms	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

