


KEMET Part Number: T350C225M035AT7301
(T350C225M035ATTR)

Tantalum, MnO2 Tantalum, Commercial Grade, T350, 2.2 uF, 20%, 35 V, Radial, Solid Tantalum, Conformal, Dipped, Lead Spacing = 2.54mm



Dimensions

D	5mm
H	8.4mm
S	2.54mm +/-0.38mm
LL	12.7mm +/-1.26mm
F	0.5mm +/-0.05mm

Packaging Specifications

Packaging:	T&R, 305mm
Packaging Quantity:	1500

General Information

Dielectric:	MnO2 Tantalum
Style:	Radial
Series:	T350
Description:	Radial, Solid Tantalum, Conformal, Dipped
Features:	Low Leakage
RoHS:	Yes
Termination:	Tin
Notes:	Longest Lead Is Positive

Specifications

Capacitance:	2.2 uF
Capacitance Tolerance:	20%
Voltage DC:	35 VDC (85C), 28 VDC (125C Surge), 0.35 V (125C Reverse)
Temperature Range:	-55/+125C
Dissipation Factor:	5%
Leakage Current:	0.6 uAmps